

A large, light blue circular graphic that serves as a background for the title. Overlaid on the bottom half of the circle is a blue line graph representing a spectrum, with several sharp peaks of varying heights.

SYSTEM **Performance**

CAMERA OVERVIEW

CAMERA DETAILS

Description	Model Number						Serial Number	
Head ▽	DU	-	888E	-	C00	-	UVB	X - 5982
Controller Card	CCI	-	24				Serial Number	C - 5986
Other:							Serial Number	
Other:							Serial Number	

▽ Sensor types are defined in Table 1 using the last letters in box Model Number.

Special Feature	(✓)
Special AR coated Window	
MgF ₂ Input	
Other (specify)	

A/D Feature		
A/D resolution	Readout Time	Readout Speed
14 bit	100nS per pixel	10MHz
14 bit	200nS per pixel	5 MHz
14 bit	333nS per pixel	3MHz
16 bit	1000nS per pixel	1MHz

CCD DETAILS

Manufacturer / Model No.	Pixels	Serial Number
E2V TECH CCD201	1024x1024, 13μm ²	10011-03-01
E2V TECH CCD97	512x512, 16μm ²	
E2V TECH CCD87	512x512, 16μm ²	
E2V TECH CCD60	128x128, 24μm ²	

▽ Table 1; Key code to define the meanings of the last letters in the Model Number

Options		
Letters	Sensor	Window
FI	Front illuminated sensor	Standard AR coated fused silica window
BV	Back illuminated sensor with 550nm AR coating	Standard AR coated fused silica window
UV	Front illuminated sensor with UV phosphor	Uncoated fused silica window
UVB	Back illuminated sensor with UV phosphor	Uncoated fused silica window

SUMMARY OF SYSTEM TEST DATA

SENSITIVITY, READOUT NOISE, BASE MEAN LEVEL AND SATURATION LEVEL

A/D Rate	EM = electron multiplication Con = conventional	Preamp setting	CCD Sensitivity ♦1 (electrons per A/D count)	Single Pixel Noise ♦2 (electrons)	Base Level ♦3 (Counts)
10 MHz 14 bit EM amplifier		2.4	24.35	60.14	403
		4.9	11.57	51.14	390
5 MHz 14 bit EM amplifier		1.0	52.4	82.27	355
		2.4	20.74	48.53	338
		4.9	9.54	39.59	315
3 MHz 14 bit EM amplifier		1.0	51.4	61.17	368
		2.4	19.71	34.3	365
		4.9	9.49	29.99	347
1 MHz 16 bit EM amplifier		1.0	19.14	33.69	401
		2.4	7.48	19.75	398
		4.9	3.6	18.0	386
3 MHz 14 bit CON amplifier		1.0	10.98	15.81	371
		2.4	4.23	11.59	363
		4.9	1.82	10.19	357
1 MHz 16 bit CON amplifier		1.0	4.06	9.3	406
		2.4	1.69	7.49	399
		4.9	0.63	5.84	395
Saturation Signal per pixel (MAX horizontal speed 14 bit EM amplifier)			143838	electrons / pixel	

LINEARITY AND UNIFORMITY

Linearity better than ♦4	1	% over 14 bits
Response Uniformity better than ♦5	0.3327	%

CCD DARK CURRENT

Minimum Dark Current Achievable ♦6	0.000097	electrons/pixel/sec		
@ Sensor Temperature of ♦7	-100.015	°C and	16	°C water cooling

DARK CURRENT DEFECTS

Hot Spots ♦8		(X, Y)	
(X , X)	(,)	(,)	(,)
(X , X)	(,)	(,)	(,)
(,)	(,)	(,)	(,)
(,)	(,)	(,)	(,)
(,)	(,)	(,)	(,)

Hot Columns ♦9	Column numbers indicated.	<input type="checkbox"/>	<input type="checkbox"/>
----------------	---------------------------	--------------------------	--------------------------

RESPONSE DEFECTS

White/Black Spots ♦10		(X, Y)	
Centroid	Number of Pixels	Centroid	Number of Pixels
(X , X)		(,)	
(X , X)		(,)	
(,)		(,)	
(,)		(,)	
(,)		(,)	
(,)		(,)	

White/Black Columns ♦11	Column numbers indicated	<input type="checkbox"/>	<input type="checkbox"/>
		<input type="checkbox"/>	<input type="checkbox"/>

Trap ♦12	(X, Y)	(<input type="checkbox"/> , <input type="checkbox"/>)
----------	--------	---------------------------------------------------------

TEST CONDITIONS

Readout Noise tested at	-75	°C with	16	°C water cooling
Base Mean Level measured at	-75	°C with	16	°C water cooling
Blemishes tested at	-75	°C with	16	°C water cooling

VERSION CONTROL INFORMATION

Hardware	POLO	CONNECTOR	DIGITAL	ANALOGUE	POWER
Version #	A	D	F	E	E
Firmware	ENGINE	EEPROM			
Version #	8.1	15			
Shipping	MCD	COF	RBF	DRIVER	
Software					
Version #	4.18.30004.0	438	38	4.30.0.0	
Testing	MCD	COF	RBF	DRIVER	
Software					
Version #	4.18.30004.0	438	38	4.30.0.0	

SYSTEM PASSED FOR SHIPPING

Test Technician	Date
PATRICK McCANN	MARCH 2011

NOTES

All tests are carried out with standard test card

Actual performance may differ slightly with supplied card, but will remain within specification

- ◆1 Sensitivity is measured in photoelectrons per A/D count from a plot of Variance [Noise squared] against Signal.
- ◆2 Readout Noise is measured for single pixel readout with the CCD in darkness at temperature indicated and minimum exposure time. Noise values will change with pre-amplifier gain selection [PAG].
- ◆3 Average electronic DC offset for CCD in darkness at temperature indicated and minimum exposure time under dark conditions and single pixel readout.
- ◆4 Linearity is measured from a plot of counts vs. signal up to the saturation point of the system. Linearity is expressed as a percentage deviation from a straight line fit. This quantity is not measured on individual systems.
- ◆5 RMS (root mean square) deviation from the average response of the CCD in full resolution image operation illuminated with uniform white light (defects not included).
- ◆6 Dark current falls exponentially with temperature. However, for a given temperature the actual dark current can vary by more than an order of magnitude from device to device. The devices are specified in terms of minimum dark current achievable rather than minimum temperature.
- ◆7 Minimum temperature achieved for thermoelectric (TE) cooler set to maximum value with water cooling.
- ◆8 A hot spot can be up to 3 pixels in size. For Grade A devices, hot spots are counted if they exhibit >50 times the maximum specified dark current at the test temperature indicated.
- ◆9 A column is considered defective if >10 pixels are affected, or if the column exhibits >2 times the maximum specified dark current at the test temperature indicated.
- ◆10 White/black spots have signals >25% above/below the average (25% contrast) with uniform illumination across the sensor.
- ◆11 White/black columns have ≥ 10 white/black spots with uniform illumination across the sensor.
- ◆12 Traps are pixels which absorb charge as it is clocked through the defective area. When the light source is switched off, the signal from the trap appears to drop off more slowly than the signal from the surrounding pixels.

ENI00453 iXon EMCCD Photo Packing List

Sales order #. 012495 Disp. Date. 23 Mar 11 Packer. *mu*

Controller card Ser No. <i>5986</i> ✓	iXon Camera Ser No. <i>5982</i> ✓	ACE-00360 Splitter/fly lead Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	3.0 Mtr iXon detector cable Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>
Software & Manuals CD User Manual: Yes <input checked="" type="checkbox"/> No <input type="checkbox"/> Type: <i>Solus</i> ✓ Version:	ACE-02029 Fly lead Sata adapter Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	2 Mtr SMB/BNC Cable 2 off Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	Power supply Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>
Disposable ESD wrist strap Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	Power supply cable Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	Mounting posts Yes <input checked="" type="checkbox"/> No <input type="checkbox"/>	